





Aqua Balloons Inflation Tips, Size Guide & Float Times

When using independently



Insert the recommended device into the mouth of the Aqua Balloon (with cover film) and inflate a little bit until the cover film peels off.




Take care regarding stickiness due to static electricity.

Peel the cover film on both sides as far as the mouth part and inflate the Aqua Balloon to the recommended size.



Peel off any remaining cover film from the mouth part, then pull the mouth part of the Aqua Balloon while twisting and make a tight knot to complete.

When using with a rubber balloon inserted



Wrap the rubber balloon on a thin plastic rod or similar and insert into the Aqua Balloon from the mouth.



Take care regarding stickiness due to static electricity.


Insert the recommended device into the mouth of the rubber balloon and inflate a little bit until the cover film peels off.

Peel the cover film on both sides as far as the mouth part and inflate the Aqua Balloon to the recommended size.




Peel off any remaining cover film from the mouthpart, then pull the mouth parts of the Aqua Balloon and rubber balloon together, and twist and make a tight knot to complete.

When using as wrapping



Cut off the top of the Aqua Balloon (with cover film) in a straight line and insert the object you want to wrap.



Use a heat sealer to seal 2cm inside of the cut line, making sure not to cause wrinkles.

Insert the recommended device into the mouth of the Aqua Balloon (with cover film) and inflate a little bit until the cover film peels off.

Peel the cover film on both sides as far as the mouth part and inflate the Aqua Balloon to the recommended size.



Do not insert sharp objects or extremely heavy objects. Doing so could cause the balloon to burst.

Peel off any remaining cover film from the mouth part, then pull the mouth part of the Aqua Balloon while twisting and make a tight knot to complete.

Aqua Balloon Size	Minimum	Maximum
125mm	130mm	★230mm
235mm	★270mm	★420mm
470mm	★650mm	★800mm